




Biofinity® family advantage.





- The broadest range of prescriptions in a monthly lens¹
- Millions of satisfied wearers worldwide²







For your single vision patients.

-  94% of patients agree that Biofinity Energys® lenses **help their eyes not feel strained**.³
-  86% of Biofinity Energys® wearers agreed that the lens makes their eyes feel **more comfortable**, even when they are on digital devices compared to their previous contact lenses.⁴
-  **Biofinity Energys®** contact lenses are the **first** and **only** contact lenses designed to help with **eye tiredness** and **dryness** associated with digital eye fatigue.⁵





For your patients with astigmatism.

-  **Biofinity® toric** is the **proven toric lens you can count on**.
-  **Over 20,000 SKUs** – more than **5x the range of other monthly toric lenses** – so you can fit virtually all your astigmatic patients in Biofinity® toric.
-  **1 out of 2** patients who wear toric frequent replacement contact lenses in Canada are **wearing a CooperVision lens**.¹²
-  **84%** of patients surveyed agreed or strongly agreed that Biofinity® toric lenses are the **best they've ever worn**.⁶

For your patients with presbyopia.

-  Balanced Progressive® Technology with 2 different optical designs and 4 distinct ADDs up to +2.50 for a **simplified, flexible and individualized fitting approach**.
-  **Biofinity® multifocal** and the **OptiExpert™** free fitting app allows for **fast, accurate and easy fitting to save valuable chair time**.⁷
-  **98%** of wearers can be **successfully fit** with Biofinity® multifocal using 2 pairs of lenses or less with OptiExpert™.⁷
-  Nearly **1 out of 2** patients who wear multifocal frequent replacement contact lenses in Canada are **wearing a CooperVision lens**.¹²

For your astigmatic presbyopes.

-  Leverages the **proven technologies** and **optical designs** of Biofinity® toric and Biofinity® multifocal.
-  **93% success rate** on initial lens fitting.⁸
-  **Over 200,000 unique prescription options**⁹ more than 46X times more prescription options than ULTRA® Multifocal for Astigmatism.¹⁰
-  Biofinity® toric multifocal can **provide correction nearly 100%** of astigmatic presbyopes.¹¹

FROM SPHERE TO SPECIALTY *Only* Biofinity®

SPHERE TORIC MULTIFOCAL

1. US industry data on file. 2. Data on file. 3. CVI Data on file 2016. Prospective, multi-center, subject-masked, bilateral, one month dispensing study in USA with Biofinity Energys in existing Biofinity sphere wearers. N=52. After 2-weeks. 4. CVI data on file, 2018. Online survey Biofinity Energys CL wearers, USA. n=200. 5. US monthly single vision lens. 6. The results of an online survey involving patients who wear Biofinity® toric contact lenses. January 2018 Biofinity® toric wearer online survey. Data on file. 7. CVI data on file 2019. Retrospective analysis; N=55 subjects (110 eyes); DV Rx +1.25D to -3.25D, ADD powers +1.25 to +2.50DS. 8. CVI Data on file 2018. Non-dispensing, subject masked, randomized, bilateral, cross-over short-term clinical evaluation. 27 astigmatic, presbyopic soft CL wearers at 2 sites (UK & US) fitted using CVI fit guide. 9. CVI data on file 2019. Based on total number of prescription option combinations (for sphere, cylinder, axis and ADD - including D & N combinations) manufactured update 10. CVI data on file 2019. B&L product specifications, US October 2019. Based on total number of prescription option combinations (for sphere, cylinder, axis and ADD - including D & N combinations) manufactured; BFTMF is made-to-order; Ultra MFfa is stocked. 11. CVI data on file 2020; Rx coverage database; 42 to 70 years ≥0.75DC. 12. Reference; CVI data on file 2020, Canada. Industry reports and internal estimates.

Innovative products to meet your patients' needs today, with a pulse on your future needs, as CooperVision® continues to invest in the Biofinity® product portfolio.

	Material	Water Content	Base Curve (mm)	Diameter (mm)	Sphere Power	Cylinder	Axis	ADD Power	Center Thickness @-3.00D	Dk	Dk/t @-3.00D	Lens Design	Handling Tint	Replacement Schedule	Wearing Schedule
Biofinity®	comfilcon A	48%	8.6	14.0	+8.00D to -12.00D (0.50D steps after ±6.00D)				0.08	128	160	Aspheric Front Surface	Softblue® Visibility Tint	Monthly	Daily wear/ extended wear/ continuous wear
Biofinity® XR	comfilcon A	48%	8.6	14.0	+8.50D to +15.00D and -12.50D to -20.00D (0.50D steps)				0.11	128	160	Aspheric Front Surface	Softblue® Visibility Tint	Monthly	Daily wear/ extended wear/ continuous wear
Biofinity Energys®	comfilcon A	48%	8.6	14.0	+8.00D to -12.00D (0.50D steps after ±6.00D)				0.08	128	160	Digital Zone Optics®	Softblue® Visibility Tint	Monthly	Daily wear/ extended wear/ continuous wear
Biofinity® toric	comfilcon A	48%	8.7	14.5	+8.00D to -10.00D (0.50D steps after ±6.00D)	-0.75, -1.25, -1.75, -2.25	10° to 180° (10° steps)		0.11	128	116	Optimized Ballast Design	Softblue® Visibility Tint	Monthly	Daily wear/ extended wear/ continuous wear
Biofinity® XR toric	comfilcon A	48%	8.7	14.5	+10.00D to +8.50D (0.50D steps)	-0.75, -1.25, -1.75, -2.25	5° to 180° (5° steps)		0.11	128	116	Optimized Ballast Design	Softblue® Visibility Tint	Monthly	Daily wear/ extended wear/ continuous wear
					+10.00D to -10.00D (0.50D steps after ±6.00D)	-2.75, -3.25, -3.75, -4.25, -4.75, -5.25, -5.75									
Biofinity® toric multifocal	comfilcon A	48%	8.7	14.5	+10.00D to -10.00D (0.50D steps after ±6.00D)	-0.75, -1.25, -1.75, -2.25, -2.75, -3.25, -3.75, -4.25, -4.75, -5.25, -5.75	5° to 180° (5° steps)	+1.00, +1.50, +2.00, +2.50	0.11	128	116	D Lens, N Lens	Softblue® Visibility Tint	Monthly	Daily wear/ extended wear/ continuous wear
Biofinity® multifocal	comfilcon A	48%	8.6	14.0	+6.00D to -10.00D (0.50D steps after -6.00D)			+1.00, +1.50, +2.00, +2.50	0.09	128	142	D Lens, N Lens	Softblue® Visibility Tint	Monthly	Daily wear/ extended wear/ continuous wear

Interested in giving your patients the Biofinity® advantage? Learn more at coopervision.ca/only-biofinity-toric

FROM SPHERE TO SPECIALTY
Only Biofinity®

