

The ideal balance of comfort and clear vision, at any distance – *Only Biofinity*[®] multifocal.



1.8 billion people globally with presbyopia.¹



Global unmet need for presbyopia correction is **45%**.¹



826 million reported near vision impairment due to no or inadequate vision correction.¹



78% of patients most commonly cited distance visual acuity as reason they preferred *Biofinity*[®] multifocal lenses.²



Biofinity[®] multifocal is rated as better for near vision than AIR OPTIX[®] Aqua Multifocal.³



Biofinity[®] multifocal is rated higher for at-arm's-length vision than AIR OPTIX[®] Aqua Multifocal.³

An easy way to fitting presbyopic patients.

Unique Technology.

Balanced Progressive[®] Technology


- Two different optical designs (D and N) utilize the processing power of the visual cortex to enhance vision
- Optimized for exceptional vision at all distances: near, intermediate, and far
- Lens zones optimized for each sphere and ADD power
- Allows for an individualized fitting for each wearer and eye

Streamlined Fitting.

- Fitting process based on eye care professionals' real-world fitting experience
- Fitting lower ADD powers is simpler than ever, by using the same D lens design for both eyes and the N lens is still available in lower ADD powers
- Fitting higher ADD powers continues to be flexible, giving you more options for greater accuracy
- Easy to use fitting guide to help maximize patients' success with our *Biofinity* multifocal lenses


D lens

- Distance vision
Spherical central zone
- Intermediate vision
Progressive zone
- Near vision
Spherical zone
- Lens edge



N lens

- Near vision
Spherical central zone
- Intermediate vision
Progressive zone
- Distance vision
Spherical zone
- Lens edge







“ I have been using CooperVision’s Biofinity® multifocal since its inception. The lens provides sharp, crisp vision and excellent fitting ability. It is our first lens we apply to our bifocal patients. It settles quickly and provides excellent visual acuity at distance and near. CooperVision provides excellent customer service and that makes my job easier. ”
 — Neil W. Draisin, OD, FCOVD

Proven comfort for high patient satisfaction.

Aquaform® Technology

- Natural and uniform wettability so the lens stays moist without the need for surface treatments or additives providing maximum comfort
- Longer siloxane chains means less silicone results in an optimum modulus, creating a softer and more flexible lens.
- Resists deposits for less build-up and increased comfort
- High oxygen transmissibility provides superb breathability for daily or continuous wear (29 nights / 30 days), helping maintain healthier corneal physiology



78% of patients preferred **Biofinity® multifocal** lenses as their lens of choice.^{2*}



BIOFINITY® MULTIFOCAL – INNOVATIVE. ADVANCED. TRUSTED.

A streamlined fitting process to fit your presbyopic patients in a high performing lens with advanced material.

	Material	Water content	Base curve (mm)	Diameter (mm)	Sphere power	ADD power	Lens design	Center thickness	Dk	Dk/t @ -3.00D	Handling tint	Replacement schedule	Wearing schedule
Biofinity® multifocal	comfilcon A	48%	8.6	14.0	+6.00 to -10.00 (0.50D steps after -6.00)	+1.00, +1.50, +2.00, +2.50	D Lens, N Lens	0.09 @ -3.00D	128	142	Sofblue® visibility tint	Monthly	Daily or extended wear up to 29 night, 30 days

NOW AVAILABLE: Inventive Digital Online fitting tool **OptiExpert™**

For fitting tips, peer testimonials and more on **Biofinity® multifocal** visit: www.coopervision.ca



CooperVision®

coopervision.ca
1 888 475 8555



*Among patients who chose to continue wearing lenses used in the study.

REFERENCES: 1. Elsevier, Global Prevalence of Presbyopia and Vision Impairment from Uncorrected Presbyopia: Systematic Review, Meta-analysis, and Modelling: <https://www.sciencedirect.com/science/article/pii/S0161642017337971> 2. Data on file. 3. Clinical evaluation of the Biofinity multifocal compared to the Air Optix® Aqua multifocal lenses (2010); results on file

© 2019 CooperVision, Inc. CooperVision, Biofinity and Aquaform are registered trademarks, and Biofinity Energys and Digital Zone Optics are trademarks of The Cooper Companies, Inc., its subsidiaries or affiliates.